


# **ELIPSE® HALF-FACE MASK** +HESPA™ A2P3 DUST (R) Filters









#### **Standards**

EN140: 1998 Mask Body EN14387: 2004 + A1: 2008 A2P3 R D CE 2797 - UKCA 0086

# **Efficiency**

P3 >99,95% for 0,3 µm particulate At 5000 ppm: Cyclohexane ( $C_6H_{12}$ ) > 35 minutes

## **Shelf Live**

5 years (mask & filters) See storage conditions on Instructions for Use. Filters are re-usable and changeable.

Mask + Filter: net (S/M) 334 g; (M/L) 342 g gross (S/M) 435 g; (M/L) 443 g Filter: net 121 g each; both net 242 g, gross 265 g

- Mask: Medical grade TPE Conforms to ISO 10993-10: 2010 for irritations. Mask body latex and silicone free, odour free. Valve Body in Nylon, Inhalation/Exhalation diaphragm in Silicone.
- 4 point adjustable elasticated head and neck strap with comfort pad in TPE. • Gas Filters: Activated carbon sealed into a ABS Shell.
- Particulate filters: Mechanical type multi-layer HESPA Synthetic media with TPE flexible overmolded / encapsulated. Particulate filters are integrated with the carbon element.

#### **Production**

United Kingdom 100% of filters NaCl Tested

	Code	Description	Quantity
63	SPR495 (S/M) SPR496 (M/L)	A2P3 Reusable Half Mask for Organic Gases, Vapours and Dust	8 pcs. per box
	SPR497	A2P3 replacement filters	5 sets of 2 pcs. per box
GVS	SPM009	Elipse High efficiency Mask Carry Case (Belt holder)	10 sets per

# **Applications - Universal gases, dust, mist and fumes**



**ECKER** 

# Weldina

W: 60 mm

Metal Fumes and Dust in confined space (gas welding)





## Construction

Paint, Moulds.





### Car & Ship Repair Epoxite, Paint,

Solvants



